

Pass and Seymour Canopy Switch Part No. 1201

Pressure Sensitive Door and Canopy Switch 15A 120VAC, 15A 250VAC



Features & Benefits

Easily accessible break-off separate or common feed.	Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
Side wire #12 and #14 AWG.	Two devices fit into the space of one.
Grounding combination devices meet NEC Requirements.	Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
For covering patents, see	

www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL Listed
Dimensions			
Product Width US	1.516 in	Product Depth US	1.344 in
Product Height US	4.031 in		
Technical Information			
Contact Configuration	N-0	Operating Cycles	30000
Contact Rating	120/250 VAC, 15 Amp	Amperage	15 A

Action	SP	Number of Poles	Single Pole
Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2