

Pass and Seymour 20A, 125V Rubber Dust-Tight Plug, Yellow Part No. 1433P

Straight Blade Rubber Plug 20amp 125volt 5-20p



Features & Benefits

Rubber body construction stands up to impacts, oils,
chemicals, heat, and weather.Floating blades allow self-alignment with contacts for a firm,
even electrical connection.Terminal screws backed-out, ready-to-wire, saving time and
money.Nickel-plated blades and contacts for long-lasting, superior
corrosion resistance.Quick-drive assembly screws allow for fast installation,
saving time and money.Self-centering cord clamps provide superior strain relief.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow	
Country Of Origin	United States	Application Sector	Commercial	
Standard	UL 498			
Dimensions				
Product Width US	1.93 in	Product Height US	2.59 in	
Listing Agencies / 3rd Party Agencies				
CSA Listed	Yes	CSA File Number	701645	
Technical Information				

Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125.0 V		