

radiant Collection radiant® Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, USB Type A/A, Gray Part No. 1597TRUSBAAGRY



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet Provides reliable ground fault protection with a trip indicator light and reset button on for easier charging, anywhere the outlet for easy, accessible troubleshooting

for convenient charging. Shares 2.0A charging capacity between both ports

Includes traditional power outlets and two USB Type-A ports Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

power to the outlet if any critical components are damaged for added protection

Equipped with proven SafeLock[™] feature which disconnects Protect children using a patented ""invisi-shutter" system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Installs quickly thanks to a redesigned side wire cavity for easier access

Can provide ground fault protection to downstream outlets through feed-thru wiring

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info Product Line Pass & Seymour Replaced by Part Number Finish Color Gray Matte Country Of Origin China Number of Receptacles 2 Construction Polycarbonate Features **USB-A Charging** GFCI, Indoor, Residential, Self-Test, Tamper-Outlet Type Application Sector Residential/Commercial Resistant, USB-Charging Warranty Type 1-Year Limited Warranty Туре Outlet Dimensions Product Width US 1.73 in 1.03 in Product Depth US Product Height US 42 in

Listing Agencies / 3	Brd Party Agencies		
CSA Listed	Yes	cULus ListingNumber	E140596
cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 50
Additional Informat	ion		
RoHS Conformant	Yes		
Technical Informati	on		
Is Tamper-Resistant	Yes	USB Amperage	2.1 A
Number of USBs	2	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Is Weather Resistant	No	Indoor/Outdoor	Indoor
Wattage	1875 W	Mounting Type	Box
Voltage	125.0 V		