

Pass and Seymour 15A/10A, 125V/250V Watertight Straight Blade Connector, Yellow Part No. 15W07



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

Features & Benefits

Rubber body construction stands up to impacts, oils,
chemicals, heat and weather.Floating blades allow self-alignment with contacts for a firm, even
electrical connection.Terminal screws backed-out, ready-to-wire, saving time
and money.Nickel-plated blades and contacts for long-lasting, superior
corrosion resistance.Compression-type cord grip provides watertight seal and
205 lb. pull out strength.Multiple ring seals between plug and connector ensures protection
from water and contaminants.

Quick-drive assembly screws allow for fast installation to save time and money.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow	
Country Of Origin	United States	Application Sector	Commercial	
Standard	CSA Listed, FSUL, UL Listed			
Dimensions				
Product Height US	1.85 in	Product Length US	4.03 in	
Technical Information				
Phase	Single	Connection	Cable	
Number of Wires	3	Amperage	10 A	

Number of Poles	3-Way	Wire Size	18 - 12 AWG
Voltage	125.0 V	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized