



Pass and Seymour  
15A, 125V Watertight Straight Blade Connector, Black  
Part No. 15W47BK



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour watertight plugs and connectors feature multiple seals to ensure protection against the environment. Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

## Features & Benefits

Rubber body construction stands up to impacts, oils, chemicals, heat and weather.

Floating blades allow self-alignment with contacts for a firm, even electrical connection.

Terminal screws backed-out, ready-to-wire, saving time and money.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Compression-type cord grip provides watertight seal and 205 lb. pull out strength.

Multiple ring seals between plug and connector ensures protection from water and contaminants.

Quick-drive assembly screws allow for fast installation to save time and money.

NEMA 4, 4X, Watertight. IP65, 66, 67.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	United States	Application Sector	Commercial
Standard	CSA Listed, FSUL, UL Listed		

### Dimensions

Product Height US	1.85 in	Product Length US	4.03 in
-------------------	---------	-------------------	---------

### Technical Information

Phase	Single	Connection	Cable
-------	--------	------------	-------

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG
Voltage	125.0 V	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized