Llegrand[®]

Pass and Seymour 15A, 250V Watertight Straight Blade Connector, Black Part No. 15W49BK

Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour watertight plugs and connectors feature multiple seals to ensure protection against the environment. Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.	Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.	Devices resist high-pressure hose down of 1,500 psi.
Color-coded sealing bushings provided for large range of cord diameters	Large ribs on body for a superior grip when mating.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black		
Country Of Origin	United States	Application Sector	Commercial		
Standard	CSA Listed, FSUL, UL Listed				
Dimensions					
Product Width US	1.85 in	Product Length US	2.62 in		
Technical Information					
Phase	Single	Connection	Cable		
Number of Wires	3	Amperage	15 A		

Number of Poles	Double Pole	Wire Size	18 - 12 AWG
Voltage	250.0 V	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized