



Hospital-Grade Tamper-Resistant Weather-Resistant 15A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade GFCI self-test CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Commercial, GFCI, Outdoor, Tamper-Resistant, Weather-Resistant	Type	Outlet

Dimensions

Product Width US	1.73 in	Product Depth US	1.13 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Outdoor
Voltage	125.0 V		