# 

#### radiant Collection radiant® Tamper-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Type A/A Outlet, Brown Part No. 2097TRUSBAA



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for Provides reliable ground fault protection with a trip indicator light and reset button on the easier charging, anywhere outlet for easy, accessible troubleshooting

Includes traditional power outlets and two USB Type-A ports for<br/>convenient charging. Shares 2.0A charging capacity between<br/>both portsSelf-tests every three seconds, ensuring continuous ground fault protection for greater<br/>safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal<br/>there is an issue and the outlet should be replaced

Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Protect children using a patented "'invisi-shutter" system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Installs quickly thanks to a redesigned side wire cavity for easier Can provide ground fault protection to downstream outlets through feed-thru wiring access

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

## Specifications

### General Info

CSA Listed	Yes	cULus ListingNumber	E140596
Listing Agencies / 3rd	Party Agencies		
Product Height US	4.2 in		
Product Width US	1.73 in	Product Depth US	1.03 in
Dimensions			
Warranty Type	1-Year Limited Warranty	Туре	Outlet
Features	USB-A Charging	Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper- Resistant, USB-Charging
Country Of Origin	China	Number of Receptacles	2
Color	Brown	Finish	Matte
Product Line	Pass & Seymour	Replaced by Part Number	

cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 81		
Additional Information					
RoHS Conformant	Yes				
Technical Information					
USB Amperage	2.1 A	Number of USBs	2		
Number of Gangs	1	Amperage	20 A		
Number of Poles	Double Pole	Indoor/Outdoor	Indoor		
Wattage	1875 W	Mounting Type	Box		
Voltage	125.0 V				