

Pass and Seymour Turnlok® 20A, 3° 480V Watertight Connector, NEMA 4X/6P, Yellow Part No. 27W76



Rated watertight for 1,500 psi high-pressurehosedown, Pass and Seymour Turnlok watertight plugs and connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.	Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.	Devices resist high-pressure hosedown of 1,500 psi.
Color-coded sealing bushings provided for large range of cord diameters	Large ribs on body for a superior grip when mating.
For Covering Patents, see www.legrand.us/patents.	

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed
Dimensions			
Product Width US	1.85 in	Product Depth US	4.03 in
Product Height US	1.85 in		
Technical Information			
Phase	Three	Number of Wires	4
Amperage	20 A	Number of Poles	3-Way

Wire Size	14 - 10 AWG	Voltage	480.0 V
Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized		