

Pass and Seymour 29W76 Watertight NEMA 4X/6P Locking Connector,Yellow Part No. 29W76



Locking Watertight Connector, 30amp 3 480volt, NEMA Configuration L16-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.	Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.	Devices resist high-pressure hose down of 1,500 psi.
Color coded sealing bushings provided for large range of cord diameters	Large ribs on body for a superior grip when mating.
Specifications	

## General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed
Dimensions			
Product Width US	2.35 in	Product Length US	4.75 in
Technical Information			
Phase	Three	Number of Wires	4
Amperage	30 A	Number of Poles	3-Way
Wire Size	12 - 6 AWG	Voltage	480.0 V

Environmental Conditions		Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,
		66, 67 (Plug & Connector only) Flammability
	UL94V0 (boxes & wiring device interiors) Operating	
	Temperature -40°C (without impact) to +60°C	
		continuous UV resistance All exposed material s
		are UV stabilized