



Quiktron
Q-Series Patch Cords, CAT6, booted, Orange, 50 FT
Part No. 576-140-050



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

Product Line	Quiktron	UPC Number	884815780520
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Type	Copper Patch Cord		

Dimensions

Product Weight US	1.25 lb	Product Length US	50.0 FT
-------------------	---------	-------------------	---------

Additional Information

RoHS Conformant	Yes
-----------------	-----