



Triple-Pole, Three Phase Switch (7803) in a NEMA 7 and 9 Enclosure for Hazardous Locations. Class I - Groups C, D Class II - Groups E, F, G. 30A, 600Vs. Slotted opening on enclosures allows for lock-out, tag-out functionality.

Features & Benefits

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Standard	UL Listed

Dimensions

Product Width US	3.375 in	Product Depth US	4.25 in
Product Height US	5.875 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17949
------------	-----	-----------------	-------

Technical Information

Amperage	30 A	Voltage	600.0 V
----------	------	---------	---------