



## Pass and Seymour Manual Controller

Part No. 7833MD



Three pole, Three Phase AC Manual Motor Controller 30 amp, 600 watts., Suitable as Motor Disconnect - 10KA @ 600VAC, 30A max Class J fuse.

### Features & Benefits

High Horsepower rating of 20HP

Constructed of glass-reinforced thermoplastic

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Gull-wing shaped brass terminal pressure clamps

UL508 and cULus Listing of individual device and assembled device within enclosure

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Aluminum
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed

#### Dimensions

Product Width US	4.5 in	Product Depth US	1.8 in
Product Height US	5.75 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

---

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Amperage	30 A
Enclosure Type	NEMA 3R	Voltage	600.0 V
Environmental Conditions	UL94 V2		

---