

Manual Control Switch 3-Pole 60A 600V



Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

| | | | |
|--------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Country Of Origin | France |
| Standard | cULus Listed | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.74 in | Product Depth US | 1.66 in |
| Product Height US | 3.26 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 135325 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|----------|------|---------|---------|
| Amperage | 60 A | Voltage | 600.0 V |
|----------|------|---------|---------|