



On-Q  
4K Premium Certified HDMI Cable, 2m  
Part No. AC4K2MBK

## 4K PREMIUM CERTIFIED HDMI CABLE



**4K**  
@ 120Hz

**HDR**

**18.6**  
Gbps

**CL3**  
IN-WALL  
RATED

The premium certified 4K (18Gbps) HDMI cable supports 4K at 60Hz. Each length is in-wall rated (CL3/FT4) and supports a high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®. Each cable bears the Premium Certification label to guarantee authenticity.

## Features & Benefits

Supports 4K at 60Hz

CL3/FT4 Rated for in-wall use

Enhanced retention clips keep the cable firmly in place

Gold Plated Connector resists corrosion and provides the highest level of signal conductivity

Enhanced Audio Return Channel (eARC): Supports high-bitrate audio formats including DTS-HD Master Audio™, DTS:X®, Dolby® TrueHD and Dolby Atmos®

## Specifications

### General Info

Product Line	On-Q	Color	Black
Finish	Matte	Country Of Origin	China

### Dimensions

Product Width US	0.87 in	Product Weight US	0.29 lb
Product Height US	10.16 in	Product Length US	7.09 in

### Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	4K 60Hz
Jacket Application	In-Wall Rated	Cable Type	Premium HDMI

---

Jacket Rating

CL3 Rated, FT4 Rated

Data Transfer Rate

18 Gbps

---

Connector Type

HDMI

Conductor Material

Gold

---

Environmental Conditions

0.9

---