



Add contemporary style, safely, to kitchens, bathrooms and more, with GFCI Outlets from the adorne Collection. Meeting Electrical Code* for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. The adorne GFCI Outlets also self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. *GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Configuration easily supports two plugs and offers the capacity of a standard 15A outlet, in a uniquely contemporary design.

Replaces any standard outlet with ease, in as little as 10 minutes.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant
Application Sector	Residential	Standard	CULUS
Warranty Type	Limited Lifetime Warranty	Type	Outlet

Dimensions

Product Width US	1.82 in	Product Depth US	1.77 in
------------------	---------	------------------	---------

Product Height US	2.66 in
-------------------	---------

Technical Information

Is Tamper-Resistant	Yes	Interrupt Rating	15 A
---------------------	-----	------------------	------

Phase	Single	Frequency Rating	60 Hz
-------	--------	------------------	-------

Trip Range	5±1 mA	Connection	Side & Back Wire
------------	--------	------------	------------------

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

NEMA Configuration Code	5-15R	Mounting Type	Box
-------------------------	-------	---------------	-----

Voltage	125.0 V	Connection Type	Internal Pressure Plates
---------	---------	-----------------	--------------------------

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---
