

## adorne Collection adorne® Plus Size Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles, Magnesium Part No. AGFTR2153M4



Add contemporary style, safely, to kitchens, bathrooms and more, with GFCI Outlets from the adorne Collection. Meeting Electrical Code\* for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. The adorne GFCI Outlets also self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. \*GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Configuration easily supports two plugs and offers the capacity of a standard 15A outlet, in a uniquely contemporary design.

Replaces any standard outlet with ease, in as little as 10 minutes.

## **Specifications**

## General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Magnesium	Finish	Frosted
Country Of Origin	China	Number of Receptacles	2
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant	Application Sector	Residential
Standard	CULUS	Warranty Type	Limited Lifetime Warranty
Туре	Outlet		

Dimensions			
Product Width US	1.82 in	Product Depth US	1.76 in
Product Height US	3.0 in		
Technical Information			
Is Tamper-Resistant	Yes	Interrupt Rating	15 A
Phase	Single	Frequency Rating	60 Hz
Trip Range	5±1 mA	Connection	Side & Back Wire
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Вох
Voltage	125.0 V	Connection Type	Internal Pressure Plates
Environmental Conditions	95% (relative humidity, non-condensing)		