

## adorne Collection adorne® 15A Tamper-Resistant Dual-Controlled Outlet, White Part No. ARCD152W10



A modern upgrade for style, safety and energy management, this tamper-resistant, dual-controlled outlet from the adorne Collection installs easily in place of an existing outlet. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Independently cut power to either plug when not in use to conserve energy.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

## Specifications

General Info			
Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Indoor, Residential, Tamper- Resistant
Application Sector	Residential	Standard	CULUS
Warranty Type	Limited Lifetime Warranty	Туре	Outlet
Dimensions			
Product Width US	1.77 in	Product Depth US	1.73 in
Product Height US	2.12 in		

Listing Agencies / 3rd Party Agencies				
cULus Listed	Yes			
Technical Information				
Is Tamper-Resistant	Yes	Phase	Single	
Connection	Side and Back Wire	Number of Wires	3	
Number of Gangs	1	Amperage	15 A	
Number of Poles	Double Pole	Wire Size	14 - 10 AWG	
ndoor/Outdoor	Indoor	NEMA Configuration Code	5-15R	
Mounting Type	Вох	Voltage	125.0 V	
Connection Type	Internal Pressure Plates	Environmental Conditions	95% (relative humidity, non-condensing)	