



adorne Collection
adorne® 20A One-Gang Pop-Out Outlet, Magnesium
Part No. ARPTR201GM2



The cleverest way to add power and style, the Pop-Out Outlet extends to offer 2-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Provides 2-plug access when extended from wall.

Installs easily in as little as 15 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety.

Disappears back into the wall with a simple push when not needed.

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-------------------|---------------------------|-------------------------|--|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | Magnesium | Finish | Frosted |
| Country Of Origin | China | Number of Receptacles | 2 |
| Features | Pop-Out | Outlet Type | Indoor, Pop-Out, Residential, Tamper-Resistant |
| Warranty Type | Limited Lifetime Warranty | Type | Outlet |

Dimensions

| | | | |
|------------------|---------|------------------|--------|
| Product Width US | 2.99 in | Product Depth US | 2.6 in |
|------------------|---------|------------------|--------|

| | |
|-------------------|---------|
| Product Height US | 4.88 in |
|-------------------|---------|

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 20 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|-------------|----------------|--------|
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
|-----------------|-------------|----------------|--------|

| | | | |
|-------------------------|-------|---------------|-----|
| NEMA Configuration Code | 5-20R | Mounting Type | Box |
|-------------------------|-------|---------------|-----|

| | | | |
|---------|---------|-----------------|--------------------------|
| Voltage | 125.0 V | Connection Type | Internal Pressure Plates |
|---------|---------|-----------------|--------------------------|

| | |
|--------------------------|---|
| Environmental Conditions | 95% (relative humidity, non-condensing) |
|--------------------------|---|
