



Pass and Seymour
Universal Cast Weatherproof Cover, 2 Gang
Part No. CA2U2681G



Universal Cast Weatherproof Cover, 2-Gang for #26, #8, #1 Openings

Features & Benefits

Two gang universal cover.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

One sku meets six application needs

2 x 3 Metal Interchangeable Inserts = 6 Combinations, #1 Toggle Switch, #8 Duplex Receptacle and #26 GFCI :

Heavy-duty die-cast zinc. Stainless steel springs.

Covers comply with NEC Section 406.8(A).

Vertical mount only

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	India	Construction	Die cast zinc, stainless steel springs
Application Sector	Commercial	Standard	UL Listed

Dimensions

Product Width US	4.6 in	Product Height US	4.6 in
------------------	--------	-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs

2

Number of Outlets 2
