



Wattstopper's CI-24 ceiling mount passive infrared occupancy sensor reduces energy waste in unoccupied building spaces by communicating occupancy to EMS and HVAC systems.

## Features & Benefits

Detection Signature Analysis eliminates false triggers; provides immunity to RFI and EMI	Digital time delay adjustment from 30 seconds to 30 minutes
Two levels of sensitivity (minimum or maximum) are selectable through the DIP switch	Multi-level Fresnel lens for superior desktop detection
LED indicates occupancy detection	BAA/TAA-compliant models available

## Specifications

### General Info

Product Line	Wattstopper	UPC Number	754182286034
Country Of Origin	China	Features	IR (Infrared), Locator Light, Motion Sensor
Switch Type	Motion Sensor	Application Sector	Commercial
Warranty Type	5-Year		

### Dimensions

Product Width US	3.0 in	Product Weight US	0.35 lb
Product Volume US	38.67 cu in	Product Depth US	3.75 in
Product Height US	2.75 in		

---

## Additional Information

---

RoHS Conformant	Yes	DesignLights Consortium Qualified System	Yes
-----------------	-----	--	-----

---

Security	Yes
----------	-----

---

## Technical Information

---

Sensor Type	Occupancy	Amperage	37 mA
-------------	-----------	----------	-------

---

Sensing Range	360 degrees, 1200 sq ft	Voltage	24.0 V
---------------	-------------------------	---------	--------

---

Connection Type	Wired
-----------------	-------

---