



Pass and Seymour
15A, 125V Extra-Hard Use Spec-Grade Corrosion-Resistant Plug, Yellow and White
Part No. CR5266X

Straight Blade Plug 2-Pole 3-Wire 15A 125V Corrosion Resistant



Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Rugged two-piece cord grip provides more uniform cord retention.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

For covering patents, see www.legrand.us/patents.

Nylon housing provides impact and chemical resistance.

Internal dust shield keeps terminals free of contaminants.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498	Type	Straight Blade

Dimensions

Product Width US	1.516 in	Product Length US	1.752 in
------------------	----------	-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	18 - 10 AWG
Voltage	125.0 V		