



Pass and Seymour
Commercial Specification Grade Switch, White
Part No. CS15AC3W



Commercial 3-Way Switch, Side-Wire, 15A 120/277V.

Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL20		

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
------------------	---------	------------------	---------

Product Height US	4.195 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Actuator	Toggle	Contact Rating	120/277V, 20Amp
----------	--------	----------------	-----------------

Amperage	15 A	Action	TP
----------	------	--------	----

Number of Poles	3-Way	Voltage	120.0 V
-----------------	-------	---------	---------
