

Pass and Seymour Commercial Specification Grade Switch, Brown Part No. CS20AC1

Commercial 1-Pole Switch, Side-Wire, 20A 120/277V.



unbreakable plates to our radiant screwless plates to our

Features & Benefits

One-piece brass alloy contact arm for reliable electrical One-piece steel strap with integral ground is plated for performance. corrosion resistance. High strength thermoplastic polycarbonate toggle resists Heavy-duty toggle bumpers for smooth and quiet operation. breaking and chipping under heavy abuse. Available with side wire or external screw-pressure-plate back Back body made of glass-reinforced nylon. Locking support and side wire models capable of accepting #14 - #10 AWG provides resistance to face and back body separation. copper or copper-clad wire. Cam designed for fast make with positive break action to Oversized silver alloy contacts for longer dependable switch minimize arcing and prolong switch life. life. Tri-drive terminal and mounting screws. For covering patents, see www.legrand.us/patents. For compatible wall plate options, from our TradeMaster

Specifications

metal wall plates, click here.

General Info

Product Line	Pass & Seymour	Color	Brown	
Country Of Origin	Mexico	Application Sector	Commercial	
Standard	UL 498/20			
Dimensions				
Product Width US	1.32 in	Product Depth US	1.073 in	

Product Height US	3.281 in					
Listing Agencies / 3rd Party Agencies						
cULus ListingNumber	140597	cULus Listed	Yes			
Technical Information						
Actuator	Toggle	Contact Rating	20Amp, 120/277Vac			
Amperage	20 A	Action	Single Pole			
Number of Poles	Single Pole	Voltage	120.0 V			