

Pass and Seymour Hard Use Specification Grade Switch, White

Part No. CSB15AC4W

Construction 4-Way Switch, Back and Side-Wire, 15A 120/277V.



Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 20		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in

Product Height US	2.375 in					
Listing Agencies / 3rd Party Agencies						
CSA Listed	Yes	cULus Listed	Yes			
Technical Information						
Contact Rating	15Amp, 120/277Vac	Closed Contact Resistance	Toggle			
Amperage	15 A	Number of Poles	4-Way			
Wattage	4 W	Voltage	120.0 V			