

## Pass and Seymour Hard Use Specification Grade Switch, Light Almond Part No. CSB20AC2LA



Construction 2-Pole Switch, Back and Side-Wire, 20A 120/277V.

#### Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

3.281 in

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch

For covering patents, see www.legrand.us/patents.

# **Specifications**

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico	
Application Sector	Residential/Commercial	Standard	UL20	
Dimensions				
Product Width US	1.32 in	Product Depth US	1.073 in	

Product Height US

# Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes		
Technical Information					
Actuator	Toggle	Contact Rating	120/277V, 20Amp		
Amperage	20 A	Action	TP		
Number of Poles	Double Pole	Voltage	120.0 V		