

On-Q 20-inch Enclosure with Screw-On Cover

Part No. EN2000



Includes self-adhesive cable identification table

This 20"" enclosure universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flex

Features & Benefits

20-in Enclosure with Screw-On Cover Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Cover included

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023067	Country Of Origin	United States
Package Quantity	1	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Туре	Enclosure
Dimensions			

Product Width US 14.25 in Product Depth US 3.6 in

Product Height US 20.0 in

Listing Agencies / 3rd Party Agencies				
CSA Listed	Yes	cULus Listed	Yes	
Additional Information				
RoHS Conformant	Yes	Product Environmental Profile	Yes	
Technical Information				
Thickness	0.1 in	Enclosure Type	Traditional	
Cable Entry	(3) top knockouts,(6) rear knockouts,(2) rectangular knockouts for 1-gang electrical box	Frame	Cold Rolled Steel	