



Pass and Seymour  
**Tamper-Resistant Floor Box Assembly - Two Gang for Wood Sub-Floors**  
Part No. FB2TRDR2N



Tamper-Resistant Floor Box Assembly, Two #8 duplex openings, Four threaded screw plugs. Includes two 3232 15A, 125A tamper-resistant duplex receptacles. Nickel. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.

Rugged diecast cover plates with durable nickel or brass finish.

Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors.

Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.

Large box flange rests on finished floor -- no adjustments needed.

Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.

Extra-deep design leaves plenty of wiring room.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Construction	Wood Floor	Application Sector	Residential/Commercial
Standard	UL Listed		

### Dimensions

Cubic Capacity	42.5 cu in
----------------	------------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Is Tamper-Resistant

Yes

Number of Outlets

2

---