



FC062LB: Standard Duty, Closed Mesh, Locking Bale (Universal Eye), Cable Diameter 0.62 - 0.74 inches, Bale Length 18-in, Mesh Length 11-in, Break Strength 1150 lbs.

Features & Benefits

Closed mesh support grips are used when the end of the cable is accessible.

Vertical runs of no more than 100 ft.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Bale Length: 18: Mesh Length: 11

Standard duty closed mesh support grips are designed for loads up to 600 lbs.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range	0.62 in	Minimum Cable Range	0.74 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 1150		