



Ortronics

1000Base T RJ45, Copper No Wave Length, 100 meters, DOM, Commercial Temperature 100% Fortinet compatible.

Part No. FG-TRAN-GC-L



1000BASE-T SFP Copper RJ45 100m Transceiver, Copper, 100m, RJ-45, Non-DDM, C-Temp

## Features & Benefits

**Guaranteed Compatible:** In System tested in over 90 OEM switches, routers and servers.

**Industry Leading Lifetime Warranty:** For more information by product line, visit our Warranty page.

**Full Service Technical Support:** Call, chat, email or meet for expert optical connectivity support.

**99.98% Reliability Rate:** Functionally, optically and environmentally tested to exact specifications.

**98% On-Time Delivery Rate:** Extensive inventory guarantees same day shipping.

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875079682
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

### Technical Information

Fiber Optic Cable Type	Passive Twinax
------------------------	----------------