

Pass and Seymour Flexcor® Support Grips Standard Duty, Split Lace, Offset Eye, Cable Diameter 0.50 - 0.61 in. Part No. FS0500F

FS0500F: Standard Duty, Split Lace, Offset Eye, Cable Diameter 0.50 - 0.61 inches, Bale Length 4-in, Mesh Length 11-in



Features & Benefits

| Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation. | Split lace support grips are designed for loads up to 600 lbs. |
|--|---|
| Vertical runs of no more than 100 ft. | They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing. |
| Support grips are woven of corrosion-resistant tinned-stainless steel wire | Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information. |

Bale Length: 4: Mesh Length: 11

Specifications

General Info

| Product Line | Pass & Seymour | Country Of Origin | Mexico |
|-----------------------|--|---------------------|--|
| Construction | Various Types of Pulling, Support and Strain Relief Grips | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |
| Technical Information | n | | |
| Maximum Cable Range | 0.5 in | Minimum Cable Range | 0.61 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 770 | | |
| | | | |