



Pass and Seymour  
**Flexcor® Support Grips Heavy Duty, Double-Eye, Cable Diameter 3.5 - 3.99 in.**  
 Part No. FSHL350UU

FSHL350UU: Heavy-Duty, Split Lace, Double-Eye, Cable Diameter 3.5 - 3.99 inches, Bale Length 10-in, Mesh Length 45-in, Break Strength 13120 lbs.



## Features & Benefits

Heavy-duty support grips feature a double weave mesh and are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 10: Mesh Length: 45

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Technical Information

Maximum Cable Range	3.5 in	Minimum Cable Range	3.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 13120		