

radiant Collection radiant® Multi-Location Master Dimmer, Tri-Color

Part No. HCL453PMMTC



Allows precise dimming control of a light or fixture. Pair with a Multi-Location Remote Dimmer to control the same fixture from another spot in the room. Part of the radiant® Collection, it also features clean lines and smooth control for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

For use with most incandescent, CFL/LED (with the exception of 0 - 10v options) and MLV dimmable bulbs. Installs easily with 3-way wiring for multi-location dimming (use with up to nine remote dimmers).

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction. finishes to match current hardware and lighting

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Can also be used in single-pole applications for solitary control.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating* required in multi-gang applications. *Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| Product Line | Pass & Seymour | Replaced by Part Number | |
|--------------------|----------------------------|-------------------------|-------------|
| Color | Ivory, Light Almond, White | Country Of Origin | China |
| Features | Indicator Lights | Switch Type | Paddle |
| Number of Switches | 1 | Application Sector | Residential |

| Standard | CSA Listed, cULus, UL Listed | Warranty Type | Limited Lifetime Warranty | |
|---------------------------------------|--|------------------|---------------------------------------|--|
| Туре | Dimmer | | | |
| Dimensions | | | | |
| Product Width US | 2.5 in | Product Depth US | 1.25 in | |
| Product Height US | 4.25 in | | | |
| Listing Agencies / 3rd Party Agencies | | | | |
| cULus Listed | Yes | | | |
| Technical Information | | | | |
| Frequency Rating | 120VAC 60 Hz | Connection | Screw Terminals | |
| Number of Gangs | 1 | Amperage | 15 A | |
| Bulb Compatibility | CFL, Incandescent, LED | Number of Poles | 3-Way, Multi-Location, Single Pole | |
| Wattage | 700 W | Mounting Type | Вох | |
| Voltage | 120.0 V | Load | Universal | |
| Environmental Conditions | Humidity: Less than 95% non condensing | | | |