



Provides recessed power & cabling connections for flat panel and TV installation.

Features & Benefits

Manages excess cable via in-wall storage, while providing slack for: convenient access to back of TV when needed

Unique brush strap cable catcher prevents cables from falling behind the wall

All contents are Black in color to blend seamlessly with TV and Wall Mount Brackets

Compatible with all TV power plugs, even right angle cords and wall warts

Kit includes: Recessed wall plate with integrated LV brush opening, junction box, 15A tamper resistant outlet and wall plate

Specifications

General Info

Product Line	On-Q	Color	White
Finish	Matte	UPC Number	804428032533
Country Of Origin	China	Receptacle Type	5-15R
Construction	High impact flame retardant plastic	Application Sector	Residential
Standard	Kit Includes UL Approved Components		

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

Technical Information

Wire Gauge	14 AWG	Cutout	1 Outlet, 1 Cable Access
Amperage	15 A	Indoor/Outdoor	Indoor
Orientation	Vertical	Number of Outlets	2
Voltage	125.0 V		
