



On-Q
In Wall TV Connection Kit with USB White
Part No. HT21USBWHV1



The In-Wall TV Connection Kit provides recessed power and cable management for a wall mounted TV. This kit manages excess cabling via in-wall storage and recessed outlet to allow TVs to mount flush to wall. Compatible with all TV Power plugs, even right angle cords and USB Type A connections. The outlet accomodates power for multiple devices like cable box, soundbar, or streaming player like Roku or Apple TV. Kit includes recessed wall plate with integrated LV brush opening, junction box, 15A tamper resistant outlet and wall plate.

Features & Benefits

Extend power to a wall mount TV without modifying the homes existing electrical wiring

Hook up a digital TV adapter, cable box, sound bar, or streaming media devices such as Apple TV™ or Roku™

Kit Contents Include: Recessed wall plate with integrated LV brush opening, junction box, 15A tamper resistant outlet and wall plate

Compatible with all TV power plugs, USB type A connections even right angle cords

Unique brush strap cable catcher prevents cables from falling behind the wall

Specifications

General Info

Product Line	On-Q	Color	White
Finish	Matte	UPC Number	804428434672
Country Of Origin	China	Receptacle Type	5-15R
Application Sector	Residential	Standard	Kit Includes UL Approved Components

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Wire Gauge	14 AWG	Cutout	2 outlets plus 2 USB Type A
------------	--------	--------	-----------------------------

Amperage	15 A	Indoor/Outdoor	Indoor
Orientation	Vertical	Number of Outlets	4
Voltage	125.0 V		
