



Pass and Seymour  
LS Series CFL/LED/Incandescent Single Pole/3-Way Slide Dimmer with Single Pole/3-Way, 3-Speed De-Hummer Fan Control, Preset, White  
Part No. LSCLDC163PWCCV4



The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)	Single pole/3-way versions
Unique integrated single pole/3-way dimmer with fan speed control	Ratings: 150W LED & CFL: 300W Incandescent: 1.6A (Fan Control): 120VAC 60Hz

Specifications

General Info			
Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Features	Combination, Fan Control, Locator Light
Switch Type	Push, Slider	Number of Switches	2
Warranty Type	Limited Lifetime Warranty		
Dimensions			
Product Width US	2.5 in	Product Depth US	1.28 in
Product Height US	4.19 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Amperage	1.6 A	Bulb Compatibility	CFL, Incandescent, LED
Number of Poles	3-Way, Single Pole	Wattage	300 W
Voltage	120.0 V		