

Decorator Slide Fan Control, Preset/3-Speed/5A



## Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive screw-pressure-plate back wire terminals eliminates wire nuts.

Can be used with patented Snap-In Light Module (sold separately).

## Specifications

### General Info

|                   |                |                    |             |
|-------------------|----------------|--------------------|-------------|
| Product Line      | Pass & Seymour | Color              | Ivory       |
| Country Of Origin | China          | Application Sector | Residential |
| Standard          | UL Listed      | Type               | Dimmer      |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                  |             |          |         |
|------------------|-------------|----------|---------|
| Operating Cycles | 100000      | Amperage | 5 A     |
| Number of Poles  | Single Pole | Voltage  | 120.0 V |