



Pass and Seymour  
Heavy Duty, Short Length, Rotating Eye, K-Type  
Part No. PS1001

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 1.000-1.240-inch, Mesh Length - 20-inch, Eye Diameter - 1 3/8-inch, Break Strength - 16,400 lbs.



## Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 20: Eye Diameter: 1-3/8

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Technical Information

Maximum Cable Range	1 in	Minimum Cable Range	1.24 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 16400		