

3-Way Lighted Switch, Back and Side-Wire, 20A 120/277V



## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-grounded clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Clear
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 20		

### Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

---

Product Height US	3.281 in
-------------------	----------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Contact Rating	20Amp, 120/277Vac	Closed Contact Resistance	Toggle
----------------	-------------------	---------------------------	--------

---

Amperage	20 A	Number of Poles	3-Way
----------	------	-----------------	-------

---

Wattage	3 W	Voltage	120.0 V
---------	-----	---------	---------

---