

400A 600V F DBL SCREW PANEL MT ORG



Features & Benefits

Nylon housing provides outstanding impact and chemical resistance. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws (available on double set screw version only) allow greater termination torque.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL, cUL		

Technical Information

Connection	Double Set Screw	Amperage	400 A
Wire Size	2/0 - 4/0	Voltage	600.0 V

Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4
--------------------------	--