

Pass and Seymour 30A 3 Pole 4 Wire Fusible Mechanical Interlock

Part No. PS430FMIR5W



Triple Pole, Four wire, Fusiable Mechanical Interlock Receptacle. 3 amp, 600 volt.

Features & Benefits

Top or Bottom feed.

End user decides at installation whether top or bottom feed is appropriate.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

No closure plug kits required.

Specifications General Info				
Country Of Origin	United States	Application Sector	Industrial	
Standard	UL Listed			
Dimensions				
Product Width US	9.13 in	Product Depth US	9.53 in	
Product Height US	24.5 in			
Listing Agencies / 3rd	Party Agencies			
cULus Listed	Yes			
Technical Information				

Phase	3	Number of Wires	4
Amperage	30 A	Number of Poles	3-Way
Voltage	600.0 V		