



Pass and Seymour
Series 16 45° Red Double Set Screw Panel Mount - Female
Part No. PS45FRBR



Pass and Seymour cam-type devices are built with top-quality materials for enhanced durability and service life, along with increased insulation protection for safety. Our angled receptacle offerings are ideal for supplying temporary electrical distribution for film and other entertainment production, theme parks, fairs, carnivals, concert venues, arenas and convention centers, mining and construction, marine shipbuilding and repair and more.

Features & Benefits

Type 3R Rated for indoor and outdoor use.

Housing is made of Santoprene: for outstanding impact and chemical resistance.

Can be retrofitted to existing locations and power distribution systems.

For covering patents, see www.legrand.us/patents.

Solid one-piece brass contacts provide superior and consistent connection under the most extreme conditions.

Intermateable and compatible with competitive cam-type products.

Brass eyelets for #10-32 mounting through bolts (bolts not provided).

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Standard	UL Listed, CSA Listed		

Dimensions

Product Width US	2.25 in
------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Amperage	400 A	Wire Size	2/0 - 4/0
----------	-------	-----------	-----------

Voltage	600.0 V	Environmental Conditions	Environmental Flammability UL94 V2 Operating Temperature Maximum continuous +75°C, minimum - 40°C without impact Enclosure NEMA Type 3R and 4
---------	---------	--------------------------	---
