

Pass and Seymour 15A, 125V Extra-Hard Use Hospital-Grade Angled Plug, Black and Clear Part No. PS5266HGAN



Straight Blade Plug 2-Pole 3-Wire 15A 125A

Features & Benefits

Angle plugs and adapters both allow for 4-position face rotation.

146159

Tri-drive assembly and cord-grip screws are standard on all angle adapters.

Angle adapter (sold separately as catalog number EHU15AN) will accommodate all Pass & Seymour EHU-style Straight Blade plugs and connectors on a retrofit basis. Simply remove the straight handle body from the plug or connector face assembly, and replace with the angle adapter.

For covering patents, see www.legrand.us/patents.

Yes

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498	Туре	Straight Blade
Dimensions			
Product Width US	1.53 in	Product Depth US	1.35 in
Product Height US	2.13 in		

cULus Listed

cULus ListingNumber

Technical Information					
Number of Wires	3	Amperage	15 A		
Number of Poles	Double Pole	Wire Size	18 - 10 AWG		
Voltage	125.0 V				