



Straight Blade Connector 2-Pole 3-Wire 15A 125A

Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Nylon housing provides impact and chemical resistance.

Rugged two-piece cord grip provides more uniform cord retention.

Internal dust shield keeps terminals free of contaminants.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|----------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL 498 | Type | Straight Blade |

Dimensions

| | | | |
|------------------|----------|-------------------|----------|
| Product Width US | 1.516 in | Product Length US | 2.638 in |
|------------------|----------|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------------|-------------|-----------|-------------|
| Number of Wires | 3 | Amperage | 15 A |
| Number of Poles | Double Pole | Wire Size | 18 - 10 AWG |
| Voltage | 125.0 V | | |
