

Pass and Seymour 30A 4 Pole 5 Wire Fusible Mechanical Interlock

Part No. PS530FMIR5W



Four pole, Five wire Fusible Mechanical Interlock Receptacle. $7.5\,\mathrm{HP}$ Standard, $20\,\mathrm{HP}$ Max. $3\,\mathrm{amp}$, $600\,\mathrm{vac}$.

Features & Benefits

Top or Bottom feed.

End user decides at installation whether top or bottom feed is appropriate.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

No closure plug kits required.

11 1			
Specifications			
General Info			
Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States		
Dimensions			
Product Width US	9.13 in	Product Depth US	9.53 in
Product Height US	24.5 in		
Listing Agencies / 3rd	Party Agencies		
cULus Listed	Yes		
Technical Information			
Amperage	30 A		