



Pass and Seymour  
MaxGrip M3 Connector, Yellow  
Part No. PS5469Y

Straight Blade Connector 2-Pole 3-Wire 20A 250V



## Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Enclosed terminals provide solid, internally-clamped connections.

High-visibility yellow and orange, or gray.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Molded finger grips promote safe, sure handling.

Hospital Grade version displays the Hospital Grade green dot.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498	Type	Straight Blade

### Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Length US	1.83 in		

### Technical Information

---

Number of Wires

3

Amperage

20 A

---

Number of Poles

Double Pole

Wire Size

18 - 10 AWG

---

Voltage

250.0 V

---