

## Pass and Seymour 15A, 250V Extra-Hard Use Hospital-Grade Angled Plug, Black and Clear Part No. PS5666HGAN



15A, 250V Extra-Hard Use Hospital-Grade Angled Plug and Clear

## Features & Benefits

Angle plugs and adapters both allow for 4-position face rotation.

Tri-drive assembly and cord-grip screws are standard on all angle adapters.

Angle adapter (sold separately as catalog number EHU15AN) will accommodate all Pass & Seymour EHU-style Straight Blade plugs and connectors on a retrofit basis. Simply remove the straight handle body from the plug or connector face assembly, and replace with the angle adapter.

For covering patents, see www.legrand.us/patents.

# Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL Listed, FSUL		

## Listing Agencies / 3rd Party Agencies

cULus Listed Yes

#### Technical Information

Phase	Single	Connection	Cable
Number of Wires	3	Amperage	15 A

Number of Poles	Double Pole	Wire Size	18 - 12 AWG
Voltage	250.0 V		