

## Pass and Seymour MaxGrip M3 Plug, Orange

Part No. PS5965O



STR BLD PLUG 3W 15A125A

## Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see www.legrand.us/patents.

## **Specifications**

General Info				
Product Line	Pass & Seymour	Color	Orange	
Country Of Origin	Mexico	Application Sector	Commercial	
Standard	UL Listed			
Dimensions				
Product Width US	1.34 in	Product Depth US	1.21 in	
Product Height US	1.83 in			
Listing Agencies / 3rd	Party Agencies			

Yes

cULus Listed

Technical Information					
Number of Wires	3	Amperage	15 A		
Number of Poles	Double Pole	Wire Size	18 - 12 AWG		
Voltage	125.0 V				