



Pass and Seymour
MaxGrip M3 Plug, Yellow
Part No. PS5965Y



Straight Blade Plug 2-Pole 3-Wire 15A 125V

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | Mexico | Application Sector | Residential/Commercial |
| Standard | UL 498 | Type | Straight Blade |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.34 in | Product Depth US | 1.21 in |
| Product Height US | 1.83 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------|----------------|-----------------|-------------|
| Connection | Wire Grounding | Number of Wires | 3 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 4 | Voltage | 125.0 V |
