



Pass and Seymour
MaxGrip M3 Connector, Yellow
Part No. PS5969Y



Straight Blade Connector 2-Pole 3-Wire 15A 125A

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498	Type	Straight Blade

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Length US	1.83 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Connection	Wire Grounding	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	4	Voltage	125.0 V
